



HYB-800TEST

Order No.: 0180188

Price upon request

PRODUCTINFOS

Multifunction tester,

for installation and testing of AHD, TVI, CVI, CVBS and IP cameras.

- Integrated colour LCD screen (touch screen)
- Diagonal screen size: 17.5 cm (7")
- Integrated cable tester
- Power is provided via enclosed power supply or integrated rechargeable 7.4 V lithium polymer battery
- RS485 interface for PTZ cameras with PELCO D protocol and PELCO P protocol
- RJ45 jack for testing UTP cables
- 12 V power supply output for camera or converter
- USB charging port
- BNC jack in/out for camera image (720p, 1080p)
- HDMI™ input and output
- Audio input and audio output via 3.5 mm jack
- Integrated micro SD card slot (for media up to 32 GB)
- Multilingual on-screen menu (OSD)
- Rubber protective frame with carrying handle
- Supplied with protective bag and carrying strap, plug-in power supply, connection cable
- Dimensions: 240 x 154 x 46 mm

- Weight: 865 g

TECHNICAL SPECIFICATIONS

HYB-800TEST

Description	multifunction tester
Type	colour LCD screen, 17.5 cm (7")
Suitable for	AHD, TVI, CVI, CVBS, IP cameras
Power supply	via encl. power supply or integrated rech. 7.4 V Li-Polymer batt., 5 Ah
Admiss. ambient temp.	-20 °C to +70 °C
Dimensions	240 x 154 x 46 mm
Weight	865 g
Connections	RS485 (PELCO D), RJ45 jack, USB port, BNC jack in/out, HDMI™ connection in/out 3.5 mm jack (audio) in/out
Packing unit	1