


LIGHT COMBI RADIO

GENERAL DESCRIPTION

Internal antenna for analogue AM/FM and digital DAB radio reception. Its compact amplifier circuit and transparent receiver element guarantee high reception quality thanks to careful design and the use of high-performance components. At the same time, the visual impact of the antenna on the car window is kept to a minimum.



DIMENSIONS



	AM/FM	DAB
Frequencies	AM: 525 - 1710 kHz / FM: 87,5 - 108 MHz	174 - 240 MHz
Power supply	+12V Phantom	+12V Phantom
Consumption	90 mA max	90 mA max
Impedance	50 Ohm	
Gain	--	8 dBi
VSWR	AM: < 2.0 / FM: < 2.0	< 2.0
Noise figure	FM: < 3.0 dB	< 2.5 dB
Polarization	Linear - Vertical	
Connectors	FAKRA Male WHITE (code B)	FAKRA Male BLACK (code A)
Cable type	RG174	RG174
Cable length	170 mm	170 mm
Mounting	Internal adhesive	
Weight	70 g	
Temperature	Working: - 40° to + 95° C / Storage: - 40° to + 105° C	
IP protection	IP41	

DISCLAIMER – Products, information, drawings, specifications and reference numbers (hereafter “contents”) discussed herein are for reference purposes only. All contents herein are provided on an “as is” basis, without warranties of any kind. The contents discussed herein remain the sole and exclusive property of MTA S.p.A. and shall not be copied, translated in whole or in part without MTA S.p.A. prior written consent. No license of any patent, copyright, mask work, trademark or any other intellectual property right is granted under this document, by implication, estoppel or otherwise. Contents may be modified and changed by MTA S.p.A. without any notice. For updates or additional information about MTA products, please contact your nearest MTA office. All brand names, trademarks and registered trademarks belong to their respective owners.