

Media Converter 1000Base-X SFP to SFP

Description

This Gigabit Ethernet Media Converter by Delock can be used to connect different optical media. For example, multimode fiber can be converted to singlemode fiber. In the SFP slots, various optional 1 Gb/s SFP modules by Delock can be used.



Item no. 86203

EAN: 4043619862030

Country of origin: China

Package: White Box

Technical details

- Connector:
2 x SFP slot for 1000Base-X SFP module (SFP modules not included)
- Data transfer rate up to 1 Gb/s
- 6 LEDs for status monitoring
- Power consumption: 2.5 W
- Operating temperature: 0° ~ 55° C
- Metal housing
- Fanless
- Dimensions (LxWxH): ca. 95 x 70 x 26 mm

Power supply specification

- Power supply type: Euro wall power plug
- Model identifier: KA0601A-0501000EU
- Input voltage: 100 - 240 V
- Input AC frequency: 50 / 60 Hz
- Input current: 0.2 A
- Output voltage / Output current / Output power: 5.0 V / 1.0 A / 5.0 W
- Average active efficiency: 75.5 %
- No-load power consumption: 0.09 W
- DC power connector: 5.5 x 2.1 mm
- Ground outside, plus inside

System requirements

- 1000Base-X SFP module

Package content

- Media Converter
- Power supply
- User manual

Images



Interface

Output:	1 x SFP jack
Input:	1 x SFP jack 1 x 5 V DC female 5,5 mm x 2,1 mm

Technical characteristics

Data transfer rate:	Gigabit Ethernet up to 1 Gbps
---------------------	-------------------------------

Physical characteristics

Housing colour:	black
Housing material:	metal
Length:	95 mm
Width:	70 mm
Height:	26 mm

Power supply

Power supply type:	Euro wall power supply
Input voltage:	AC 100 - 240 V / 50 - 60 Hz / 0.2 A
Power supply output:	5.0 V / 1.0 A
Power supply connector:	DC male 5.5 mm x 2.1 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

