

ST= ICT Test Probe

mm [inch]





ST1800 CG04 X

Minimum centers:	4.57 (.180)
Full travel:	6.35 (.250)
Working travel:	4.40 (.173)
Current rating:	6 - 8 A (continuous)
Probe resistance:	< 20 mΩ
Plunger material:	BeCu - Gold Plated
Barrel material:	P. Bronze - Gold Plated
Spring material:	MW - Gold Plated

Operating temperature: -30 °C up to +100 °C
(-22 °F up to +212 °F)

Spring force at working stroke: 3.0 N (10.8 oz)

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	Sz. A.	2024. 10. 02.
Drawed		
Checked		

Note

Catalog Item: ST1800 CG04 X


Drawing No.:

A4 SHEET 2 OF 1

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE

ST= ICT Test Probe

mm [inch]



Tools for the Test Probe

Tool Handle:	TH1
Universal bit:	TBP20000
Insertion/Extraction Bit:	TBP18770

Tools for the Receptacle

Tool Handle Insertion:	TH1
Tool Handle Extraction:	TH2
Insertion Bit:	TBR18735
traction Bit:	TBR18770

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	Sz.A.	2024. 10. 02.
Drawed		
Checked		

Note

Catalog Item:
ST1800 CG04 X

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE