

Antenna Cable N plug > RP-SMA plug CFD400 LLC400 10 m low loss

Description

This high-quality coaxial cable ensures a reliable connection of components of the radio frequency technology. It is characterised by a **very low attenuation**. Thanks to the **waterproof** N connector, this cable is ideal for outdoor use.



Item no. 13028

EAN: 4043619130283

Country of origin: Taiwan,
Republic of China

Package: White Box

Technical details

- Connectors:
1 x N plug waterproof >
1 x RP-SMA plug
- Impedance: 50 Ohm
- Cable type: CFD400, LLC400
- Cable type: coaxial
- Cable attenuation:
0.3 dB @ 3.0 GHz per meter
0.48 dB @ 6.0 GHz per meter
- Cable diameter: ca. 10.5 mm
- Smallest bending radius: 51.5 mm
- Cable colour: black
- Length incl. connectors (L): ca. 10 m

System requirements

- Device with one free N and RP-SMA port

- Antenna cable



Interface

Connector 1:	1 x RP-SMA plug
Connector 2:	1 x N male

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable type:	CFD400, LLC400
Cable attenuation:	0.30 dB @ 3.0 GHz 0.48 dB @ 6.0 GHz
Cable colour:	black
Cable length:	10 m
Smallest bending radius:	51.5 mm
Cable diameter:	10.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

