






Seria 44 CE - Wodoszczelne puszki połączeniowe natynkowe zgodne z ANSI/UL 50 i wykonane z wysokowydajnych technopolimerów. Seria obejmuje IP56 z gładkimi ściankami i płaskimi skręcanymi pokrywami, (GWT 960°C).

Klasa Izolacji	II (zgodnie z normami IEC 61140)	Kolor	Szary RAL 7035
Ochrona IP	IP56	Materiał	Technopolimerowy GWPLAST 75
Odporność na wstrząsy	IK08	Wymiary wewnętrzne LxHxD (mm)	190x140x70
Maks. Ø otworów, możliwa	37 mm	Śruby pokryw (liczba i typ)	4 izolacja, plombowane, na zawias
Zastosowanie	Do zastosowań specjalnych	Próba rozżarzonym drutem	960 °C
Pokrywka	Płaska wkręcana	Temperatura robocza	-25 +50 °C
Electrocod	02211	Twardość kulkowa	75 °C
Moment dokręcania moment dokręcania śrub	1.8 NM	Ściany	Gładki
Wypożyczenie dodatkowe do przywrócenia izolacji	GW44621, GW44622		

BEHAVIOUR WITH CHEMICAL AND ATMOSPHERIC AGENTS

Saline solution	Acids		Bases		Solvents				Mineral oil	UV rays
	Concentrated	Diluted	Concentrated	Diluted	Hexane	Benzol	Acetone	Alcohol		
Resistant	Limited resistance	Resistant	Resistant	Resistant	Limited resistance	Not resistant	Not resistant	Limited resistance	Limited resistance	Limited resistance

DIMENSIONAL



TECHNICAL SYMBOLOGY

EN 61140
II (zgodnie z normami IEC 61140)

IP

IP56

IK


IK08

GWT

960 °C

INSTALLATION

-25°C min
+50°C max
-25 +50 °C



STANDARDS/APPROVALS

CE UK CA

