




Pressure transmitter with ceramic measuring cell

PA-,10BRBN14-A-ZVG/US/ IV



1 ventilation



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1				
Measuring range	0...0.1 bar	0...100 mbar	0...1.45 psi	0...40.16 inH2O	0...10 kPa
Process connection	threaded connection 1/4" NPT external thread internal thread:M5				

Application

Special feature	Gold-plated contacts			
Application	for industrial applications			
Media	liquids and gases			
Medium temperature [°C]	-25...90; (on request: -40...90 °C)			
Min. bursting pressure	30000 mbar	435 psi	12030 inH2O	3000 kPa
Pressure rating	4000 mbar	58 psi	1606 inH2O	400 kPa
Type of pressure	relative pressure			

Electrical data

Operating voltage [V]	9.6...32 DC
Min. insulation resistance [MΩ]	100; (500 V DC)
Protection class	III
Reverse polarity protection	yes

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal
Number of analogue outputs	1
Analogue current output [mA]	4...20



Pressure transmitter with ceramic measuring cell

PA-,10BRBN14-A-ZVG/US/ IV

Max. load	[Ω]	720; (Ub = 24 V; (Ub - 9,6 V) / 20 mA)				
Overload protection		yes				
Measuring/setting range						
Measuring range		0...0.1 bar	0...100 mbar	0...1.45 psi	0...40.16 inH2O	0...10 kPa
Accuracy / deviations						
Repeatability	[% of the span]	< 0,2; (with temperature fluctuations < 10 K)				
Characteristics deviation	[% of the span]	< ± 0,5 (BFSL) / < ± 1 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting)				
Long-term stability	[% of the span]	< ± 0,1; (per 6 months)				
Temperature coefficient zero point	[% of the span / 10 K]	< ± 0,5; (0...80 °C)				
Temperature coefficient span	[% of the span / 10 K]	< ± 0,5; (0...80 °C)				
Response times						
Step response time analogue output	[ms]	3				
Operating conditions						
Ambient temperature	[°C]	-25...80				
Storage temperature	[°C]	-40...100				
Protection		IP 68				
Tests / approvals						
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD				
	EN 61000-4-3 HF radiated	30 V/m				
	EN 61000-4-4 Burst	2 kV				
	EN 61000-4-6 HF conducted radiation of interference	10 V				
	CISPR 25 immunity	according to the automotive directive 2004/104/EC				
	ISO 11452-2 HF radiated	100 V/m				
	ISO 7637-2 pulse	severity level 3				
	Shock resistance	DIN EN 60068-2-27	50 g (11 ms)			
Vibration resistance	DIN EN 61373	category 3				
	DIN EN 60068-2-6	20 g (10...2000 Hz)				
MTTF	DIN EN 61373	category 2				
	[years]	555				
UL approval		File number UL	E174189			
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request				
Mechanical data						
Weight	[g]	210.1				
Housing		cylindrical				
Dimensions	[mm]	Ø 30 / L = 79.5				
Materials		stainless steel (316L/1.4404); FKM; PA; EPDM/X				
Materials (wetted parts)		stainless steel (303/1.4305); ceramics; FKM				

PX3289



Pressure transmitter with ceramic measuring cell

PA-,10BRBN14-A-ZVG/US/ IV

Min. pressure cycles	100 million
Tightening torque [Nm]	50; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection	threaded connection 1/4" NPT external thread internal thread:M5
Restrictor element integrated	no (can be retrofitted)

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT analogue output
 colours to DIN EN 60947-5-2
 Core colours :
BN = brown
WH = white