

Antenna WiFi 5.8 GHz RP-SMA plug 3 dBi omnidirectional with connection cable RG-174 3 m with tilt joint with magnetic base black

Description

This WiFi 5.8 GHz antenna by Delock allows the usage of WiFi frequency range 5.15 GHz to 5.85 GHz indoors.



Item no. 10038

EAN: 4043619100385

Country of origin: China

Package: Box

Technical details

- Connector: 1 x RP-SMA plug
- Frequency range: 5.15 GHz - 5.85 GHz
- Antenna gain: 3 dBi
- Impedance: 50 Ohm
- VSWR: 1.5:1
- Cable type: RG-174
- Cable attenuation: 3 dB @ 5000 MHz per meter
- Cable colour: black
- Cable length: ca. 3 m
- Polarisation: linear, vertical
- Operating temperature: -40 °C ~ 70 °C
- Housing material: ABS
- Colour: black
- Dimensions:
 - antenna (LxWxH): ca. 196.0 x 48.1 x 8.5 mm
 - base (DxH): ca. 61 x 32 mm

System requirements

- Device with a free RP-SMA jack

Package content

- Antenna

General

Suitable for indoor:	yes
----------------------	-----

Interface

Connector:	1 x RP-SMA plug
------------	-----------------

Technical characteristics

Frequency range:	5150 - 5850 MHz
Antenna gain:	3 dBi
Impedance:	50 Ohm
Operating temperature:	-40 °C ~ 70 °C
VSWR:	< 1.5

Physical characteristics

Antenna type:	dipol antenna
Cable category:	coaxial
Cable type:	RG-174
Cable length:	3 m
Length:	196 mm
Height:	8.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

