




RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
A0		20240529	Initial Release	
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

Material:

- Item ① Lever: Thermoplastic (UL 94-HB), Black
- Item ② Terminal body: Thermoplastic (UL 94V-0), Black
- Item ③ Terminal cover: Thermoplastic (UL94V-0), Black
- Item ④ Terminal: Copper alloy, Tin plated over Nickel plated

Electrical:

- Voltage rating: 300 VAC
- Current rating: 6A
- Solid wire(AWG): 16-22
- Stranded wire(AWG): 16-22
- Wire strip length: 8 mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +105°C
- Critical dimension: ▲
- Matching Pin: D=1.0mm

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		GB001 Series without switch pin					
PART NO.	GB001xx0x000G			DWG NO.	8GB0001-001		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Rhine 20250410	Rhine 20250410		UNIT: mm	X.X	±0.50
					SCALE: 2:1	X.XX	±0.30
					SHEET: 01/01	REV.: A0	X°