

Antenna Cable N jack bulkhead to I-PEX Inc., MHF® I plug 1.37 13 cm thread length 22 mm splash proof

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.

Through an inside located groove embedded in the base plate and the seal on the N base, a splash-proof connection to a device is achieved.



Item no. 89430

EAN: 4043619894307

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x N jack bulkhead >
 - 1 x I-PEX Inc., MHF® I plug
- Thread length: 22 mm
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: 1.37
- Cable attenuation: 2.5 dB @ 2.4 GHz per meter
- Cable colour: black
- Smallest bending radius: 9 mm
- Length incl. connectors (L): ca. 13 cm

System requirements

- Device with one free N or I-PEX Inc., MHF® I port

Package content

- Antenna cable
- Nut and Locking Ring

Images



Interface

Connector 1:	1 x N female
Connector 2:	1 x I-PEX Inc., MHF® I plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Cable category:	coaxial
Cable type:	1.13
Cable attenuation:	2.5 dB @ 2.4 GHz per meter
Cable colour:	black
Cable length incl. connectors:	13 cm
Cable diameter:	1.37 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

