

PBMN low pressure - Configurator


PBMN-2#####2##0#0

Overview

- Excellent accuracy and active temperature compensation for precise pressure measurements
- Measuring range from -0.1 ... 0.1 bar up to 0 ... 40 bar
- Universal field of applications due to robust stainless steel housing
- Optionally available with Ex certification (4 ... 20 mA output)
- Absolute pressure, relative pressure and vacuum measurement
- External programming of zero point and span with FlexProgrammer 9701



Picture similar



Technical data

Performance characteristics

Pressure type	Absolute Relative (gauged)
Compensated temperature range	-40 ... 85 °C
Long term stability	≤ 0.1 % FSR/a, measuring range > 1 bar ≤ 1 mbar, measuring range ≤ 1 bar
Max. measuring error	± 0.1 % FSR ± 0.25 % FSR Including zero-point and span error, non-linearity (by terminal base line), hysteresis and non-repeatability (EN 61298-2) For turndown, multiply this value by the applied turndown ratio
Max. measuring span	40 bar
Max. turndown ratio	5 : 1
Measuring range	-1 ... 40 bar
Standard error of measurement (BFSL)	± 0.04 % FSR ± 0.1 % FSR Including non-linearity, hysteresis and non-repeatability according BFSL
Min. measuring span	0.1 bar
Rise time (10 ... 90 %)	≤ 5 ms
Temperature coefficient	≤ 0.03 % FSR/10 K, measuring span ≤ 0.03 % FSR/10 K, zero point

Process conditions

Process temperature	-40 ... 120 °C
Process pressure	Refer to section "Operating conditions"

Process connection

Connection variants	Refer to section "Dimensional drawings"
Wetted parts material	AISI 316L (1.4404)
Wetted parts material, membrane	AISI 316L (1.4435)

Process connection

Wetted parts material, gas-ket	NBR, optional FKM, optional, gaskets require a minimum ambient temperature of -20 °C and a minimum medium temperature of -25 °C
--------------------------------	--

Ambient conditions

Operating temperature range	-40 ... 85 °C
Storage temperature range	-40 ... 85 °C
Degree of protection (EN 60529)	IP 65, with connector DIN EN 175301-803 A (DIN 43650 A), 4-pin IP 67, with cable outlet IP 67, with connection head IP 67, with connector M12-A, 4-pin
Insulation resistance	> 100 MΩ, 500 V DC
Bump (EN 60068-2-27)	100 g / 2 ms, 4000 impulses per axis and direction
Shock (EN 60068-2-27)	50 g / 11 ms, 100 g / 6 ms, 10 impulses per axis and direction
Vibration (sinusoidal) (EN 60068-2-6)	1.5 mm p-p (10 ... 58 Hz), 10 g (58 Hz ... 2 kHz), 10 cycles (2.5 h) per axis
Vibration, broad-band random (EN 60068-2-64)	0.1 g ² / Hz, > 10 gRMS (20 Hz ... 1 kHz), 30 min. per axis

Output signal

Current output	4 ... 20 mA, 2-wire 20 ... 4 mA, 2-wire
Voltage output	0 ... 10 V, 3-wire 0 ... 5 V, 3-wire 0.5 ... 4.5 V, 3-wire 1 ... 5 V, 3-wire 10 ... 0 V, 3-wire
Load resistance	≥ 5 kΩ
Short circuit protection	Yes

PBMN low pressure - Configurator

PBMN-2#####2##0#0

Technical data

Output signal

Shunt resistance	$R_s \leq (V_s - 8 \text{ V})/0.0205 \text{ A}$ $R_s \leq 750 \text{ } \Omega$, $V_s = 24 \text{ V}$
------------------	--

Housing

Style	Compact transmitter
Overall size	Refer to section "Dimensional drawings"
Material	AISI 316L (1.4404)

Electrical connection

Connector	DIN EN 175301-803 A (DIN 43650 A), 4-pin M12-A, 4-pin
Cable gland	Cable $\varnothing$ 8 ... 10, stainless steel
Cable outlet	1.5 m, 3-wire, shielded

Power supply

Voltage supply range	13 ... 30 V DC , with voltage output 8 ... 30 V DC , with current output
----------------------	---

ATEX II 1/2G Ex ia IIC T4/T6 Ga/Gb

Please note	For the application in Ex zone you have to respect the conditions mentioned in the type examination certificate (SEV 11 ATEX 0129 / IECEx SEV 22.0006). You will find the relevant certificates and instructions at www.baumer.com
Maximum values for barrier selection, Ui	30 V DC , max.
Maximum values for barrier selection, Ii	100 mA
Maximum values for barrier selection, Pi	750 mW
Internal capacitance, Ci	58 nF
Internal inductance, Li	0.22 μ H

ATEX II 1D Ex ia IIIC T (200) 107°C IP6X Da

Please note	For the application in Ex zone you have to respect the conditions mentioned in the type examination certificate (SEV 11 ATEX 0129 / IECEx SEV 22.0006). You will find the relevant certificates and instructions at www.baumer.com
-------------	--

ATEX II 1D Ex ia IIIC T (200) 107°C IP6X Da

Degree of protection for cable accessories	IP 65
Maximum values for barrier selection, Ui	30 V DC , max.
ATEX II 1G Ex ia IIC T4/T6 Ga	
Please note	For the application in Ex zone you have to respect the conditions mentioned in the type examination certificate (SEV 11 ATEX 0129 / IECEx SEV 22.0006). You will find the relevant certificates and instructions at www.baumer.com
Maximum values for barrier selection, Ui	30 V DC , max.
Maximum values for barrier selection, Ii	100 mA
Maximum values for barrier selection, Pi	750 mW
Internal capacitance, Ci	58 nF
Internal inductance, Li	0.22 μ H

Compliance and approvals

EMC	EN 61000-6-3 2014/30/EU (EMC) 2014/34/EU (EX)
Explosion protection	ATEX II 1/2G Ex ia IIC T4/T6 Ga/Gb ATEX II 1D Ex ia IIIC T (200) 107 °C IP6X Da ATEX II 1G Ex ia IIC T4/T6 Ga

Operating conditions

Measuring range (bar)							Proof pressure (bar)	Burst Pressure (bar)
0 ... 0,1 0 ... 0,16 0 ... 0,25							1	2
-0,1 ... 0,1 -0,2 ... 0,2 -1 ... 0	-1 ... 0,6	0 ... 0,4	0 ... 0,6	0 ... 1			3	6
-1 ... 1,5	-1 ... 3	-1 ... 5	0 ... 1,6	0 ... 2	0 ... 2,5	0 ... 4	15	30
	-1 ... 9	-1 ... 15	0 ... 6	0 ... 10	0 ... 16	0 ... 20	60	120
		-1 ... 24	0 ... 25				70	140
		-1 ... 39	0 ... 40				135	270

PBMN low pressure - Configurator


PBMN-2#####2##0#0

Operating conditions


Explosion protection (with 4 ... 20 mA output signal only)	Connectors [code]	Order key
ATEX II 1G Ex ia IIC T4/T6 Ga	M12-A [14]	PBMN-#####A114#####1#
	Connection head [54]	PBMN-#####A154#####1#
ATEX II 1D Ex ia IIIC T (200) 107 °C IP6X DA	M12-A [14]	PBMN-#####A1#####1#
	Connection head [54] DIN EN 175301-803 A [44]	
ATEX II 1/2G Ex ia IIC T4/T6 Ga/Gb	DIN EN 175301-803 A [44]	PBMN-#####A144#####1#

Dimensional drawings (mm)


Housing




Housing with connector M12-A, 4-pin



Housing with connector DIN EN 175301-803 A (DIN 43650 A), 4-pin




Housing with cable outlet, 3-wire, 1.5 m length




Field housing with cable gland

Dimensional drawings (mm)


Process connection




G30-02
G 1/4 B EN 837-1 (BCID: G30)




G31-03
G 1/2 B EN 837-1 (BCID: G31)




N01-04
1/4-18 NPT (BCID: N01)




N02-05
1/2-14 NPT (BCID: N02)




G50-06
G 1/4 A DIN 3852-E (BCID: G50)



G51-09
G 1/2 A DIN 3852-E (BCID: G51)



G51-19
G 1/2 A DIN 3852-E, hole Ø 10 mm (BCID: G51)



G21-12
G 1/4 A ISO 228-1 female thread (BCID: G21)

PBMN low pressure - Configurator

PBMN-2#####2##0#0

Electrical connection

Output signal	Equivalent circuit	Electrical connection	Function	Pin assignment
4 ... 20 mA (2-wire)			+Vs	1
			Iout	3
			Frame Ground	Plug thread
			n.c.	2, 4
			+Vs	1
			Iout	2
			Frame Ground	Grounding lug
			n.c.	3
			+Vs	1
			Iout	2
			Frame Ground	Shield
			n.c.	3, 4
			+Vs	RD
			Iout	BU
			Frame Ground	Shield
			n.c.	WH
0 ... 10 V (3-wire)			+Vs	1
			Uout	2, 4
			GND (0 V)	3
			Frame Ground	Plug thread
			+Vs	1
			Uout	3
			GND (0 V)	2
			Frame Ground	Grounding lug
			+Vs	1
			Uout	3
			GND (0 V)	2
			Frame Ground	Shield
			n.c.	4
			+Vs	RD
			Uout	WH
			GND (0 V)	BU
			Frame Ground	Shield

Ordering information

Ordering key - Configuration possibilities see website

	PBMN	-	2	#	###	#	##	##	##	2	#	#	0	#	0
Product	PBMN														
Housing material															
Stainless steel 1.4404 AISI 316L				2											
Accuracy															
±0.25 % FS					4										
±0.10 % FS					5										

PBMN low pressure - Configurator

PBMN-2#####2##0#0

Ordering information

Ordering key - Configuration possibilities see website

	PBMN	-	2	#	###	#	##	##	##	2	#	#	0	#	0
Measuring range															
0 ... 0,1 bar (EN)						B08									
0...0,16 bar (EN)						B09									
0 ... 0.25 bar (EN)						B10									
0 ... 0.4 bar (EN)						B11									
0...0,6 bar (EN)						B12									
0 ... 1 bar (EN)						B15									
0 ... 1,6 bar (EN)						B16									
0 ... 2 bar (EN)						B17									
0 ... 2.5 bar (EN)						B18									
0 ... 4 bar (EN)						B19									
0...12 bar (EN)						B1K									
-1 ... 39 bar (EN)						B1L									
0 ... 6 bar (EN)						B20									
0 ... 10 bar (EN)						B22									
0 ... 16 bar (EN)						B24									
0 ... 20 bar (EN)						B25									
0 ... 25 bar (EN)						B26									
0 ... 40 bar (EN)						B27									
-0,1...0,1 bar (EN)						B2H									
-0,2...0,2 bar (EN)						B4G									
-0,6...0 bar (EN)						B58									
-1 ... 0 bar (EN)						B59									
-1 ... 0,6 bar (EN)						B72									
-1 ... 1 bar (EN)						B73									
-1 ... 1,5 bar (EN)						B74									
-1...2 bar (EN)						B75									
-1 ... 3 bar (EN)						B76									
-1 ... 5 bar (EN)						B77									
-1 ... 9 bar (EN)						B79									
-1 ... 15 bar (EN)						B81									
-1 ... 24 bar (EN)						B82									
0...5 bar (EN)						B98									
Kind of pressure															
Relative (gauged)														R	
Absolute														A	
Output signal															
20...4 mA														A0	
4...20 mA														A1	
0...10 V														A2	
1...5 V														A3	
0...5 V														A4	
0.5...4.5 V														A5	
10...0 V														A7	
Output Connection															
M12-A, 4-pin														14	
DIN EN 175301-803 A (DIN 43650 A), 4-pin														44	
Cable outlet 1.5 m, 3-wire, shielded														53	
Connection head, cable gland IP67														54	

PBMN low pressure - Configurator

PBMN-2#####2##0#0

Ordering information

Ordering key - Configuration possibilities see website

	PBMN	-	2	#	###	#	##	##	##	2	#	#	0	#	0
Process connection															
G 1/4 B EN 837-1 (G30)										02					
G 1/2 B EN 837-1 (G31)										03					
1/4-18 NPT (N01)										04					
1/2-14 NPT (N02)										05					
G 1/4 A DIN EN ISO 1179-2 (3852-E) (G50)										06					
M20 × 1.5 ISO 261 / ISO 965 (M08)										07					
G 1/2 A DIN EN ISO 1179-2 (3852-E)(G51)										09					
G 1/4 A ISO 228-1 female thread (G21)										12					
G 1/2 A DIN EN ISO 1179-2 (3852-E)										19					
pressure channel Ø 10 mm (G52)															
G 1/4 B EN 837-1 with integrated damping element (P ≤ 600 bar) (G30)										22					
G 1/2 B EN 837-1 with integrated damping element (P ≤ 600 bar) (G31)										23					
1/4-18 NPT with integrated damping element (P ≤ 1000 bar) (N01)										24					
1/2-14 NPT with integrated damping element (P ≤ 1000 bar) (N02)										25					
G 1/4 A DIN EN ISO 1179-2 (3852-E) pressure channel Ø 0,6 mm (G50)										26					
G 1/2 A DIN EN ISO 1179-2 (3852-E) with integrated damping element										29					
Process connection material															
Stainless steel 1.4404 AISI 316L										2					
Seal															
None													0		
NBR standard													1		
FKM													3		
Oil filling															
Standard oil													1		
NSF H1 listed (FDA approved)													2		
Display															
Without display														0	
Explosion protection															
Without															0
ATEX according to SEV 11 ATEX 0129															1
Approvals															
Standard approvals															0