
SPT=Step Probe

mm [inch]





SPT1000 RL118 N

Minimum centers:	2.54 (.100)
Full travel:	4.40 (.173)
Working travel:	3.50 (.138)
Current rating:	3 - 5 A
Probe resistance:	< 20 mΩ
Plunger material:	BeCu - Gold Plated
Barrel material:	Brass - Gold Plated
Spring material:	MW - Gold Plated

Operating temperature: -40 °C up to +120°C
(-40 °F up to +248 °F)

Spring force at working stroke: 1.50 N (5.4 oz)

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	PGY	2024. 06. 14.
Drawed		
Checked		

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

Note

Catalog Item:
SPT1000 RL118 N


Drawing No.:

A4 SHEET 2 OF 1

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE

SPT=Step Probe

mm [inch]



Tools for the Test Probe

Tool Handle:	TH3
Adjustable Torque Handle:	TTS01
Insertion/Extraction Bit:	TBT10072

Tools for the Receptacle

Tool Handle Insertion:	TH1
Tool Handle Insertion/Extraction:	TH2
Insertion Bit:	TBR10035
Extraction Bit:	TBR10070

© COPYRIGHT 2023
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	PGY	2024. 06. 14.
Drawed		
Checked		

Note

Catalog Item:
SPT1000 RL118 N

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE