




Flush pressure sensor with analogue display

PG-,10BREA01-MFRKG/US/ /P



ACS CRN EC 1935/2004 EHEDG Tested FCM UK CA

Product characteristics			
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1		
Measuring range	-0.005...0.1 bar	-5...100 mbar	-2...40.15 inH2O
Process connection	threaded connection G 1 external thread sealing cone Attention: The unit must only be installed in a process connection for G1 sealing cone.; The G1A sealing cone of the unit is only suited for adapters with metal end stop.		
Application			
Special feature	Gold-plated contacts		
Application	flush mountable for the food and beverage industry		
Media	viscous media and liquids with suspended particles; liquids and gases		
Medium temperature [°C]	-25...125; (145 max. 1h)		
Min. bursting pressure	30000 mbar	12043 inH2O	
Min. bursting pressure [MPa]	3		
Pressure rating	4000 mbar	1605 inH2O	
Pressure rating [MPa]	0.4		



Flush pressure sensor with analogue display

PG-,10BREA01-MFRKG/US/ /P

Type of pressure	relative pressure		
MAWP (for applications according to CRN) [bar]	4		
Electrical data			
Operating voltage [V]	18...32 DC		
Current consumption [mA]	< 70; (24 V)		
Min. insulation resistance [MΩ]	100; (500 V DC)		
Protection class	III		
Reverse polarity protection	yes		
Power-on delay time [s]	6		
Measuring principle	hydrostatic		
Integrated watchdog	yes		
Inputs / outputs			
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1		
Outputs			
Total number of outputs	2		
Output signal	switching signal; analogue signal; (configurable)		
Electrical design	PNP/NPN		
Number of digital outputs	1		
Output function	normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC [V]	2		
Permanent current rating of switching output DC [mA]	250		
Switching frequency DC [Hz]	50		
Number of analogue outputs	1		
Analogue current output [mA]	4...20, invertible; (scalable)		
Max. load [Ω]	(Ub - 10 V) / 20 mA		
Short-circuit protection	yes		
Type of short-circuit protection	pulsed		
Overload protection	yes		
Measuring/setting range			
Measuring range	-0.005...0.1 bar	-5...100 mbar	-2...40.15 inH2O
Set point SP	-4.8...160 mbar	-1.95...64.25 inH2O	
Reset point rP	-5...159.8 mbar	-2.05...64.15 inH2O	
Analogue start point	-5...135 mbar	-2...54.2 inH2O	
Analogue end point	20...160 mbar	8.05...64.25 inH2O	
In steps of	0.1 mbar	0.05 inH2O	
Accuracy / deviations			
Switch point accuracy [% of the span]	< ± 0,5; (Turn down 1:1)		
Repeatability [% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)		
Characteristics deviation [% of the span]	< ± 0,5; (Turn down 1:1 , linearity, incl. hysteresis and repeatability , limit value setting to DIN EN IEC 62828-1)		
Linearity deviation	< ± 0,25; (Turn down 1:1)		



Flush pressure sensor with analogue display

PG-,10BREA01-MFRKG/US/ /P

	[% of the span]	
Hysteresis deviation		$< \pm 0,2$; (Turn down 1:1)
	[% of the span]	
Long-term stability		$< \pm 0,1$; (Turn down 1:1; per year)
	[% of the span]	
Temperature coefficient zero point		$< \pm 0,1$; (0...70 °C)
	[% of the span / 10 K]	
Temperature coefficient span		$< \pm 0,2$; (0...70 °C)
	[% of the span / 10 K]	
Response times		
Response time	[ms]	< 10
Damping process value dAP	[s]	0.01...30
Damping for the analogue output dAA	[s]	0.01...30
Step response time analogue output	[ms]	25
Operating conditions		
Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-5 Surge	0,5/1 kV
	EN 61000-4-6 HF conducted	10 V
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	100
Note on approval		factory certificate available as download at www.factory-certificate.ifm
Mechanical data		
Weight	[g]	562.7
Dimensions	[mm]	153 x 100 x 57
Materials		stainless steel (316L/1.4404); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm
Materials (wetted parts)		ceramics (99.9 % Al ₂ O ₃); stainless steel (316L/1.4435); surface characteristics: Ra < 0,4 / Rz 4; PTFE
Min. pressure cycles		100 million
Process connection		threaded connection G 1 external thread sealing cone Attention: The unit must only be installed in a process connection for G1 sealing cone.; The G1A sealing cone of the unit is only suited for adapters with metal end stop.



Flush pressure sensor with analogue display

PG-,10BREA01-MFRKG/US/ /P

Displays / operating elements		
Display	Display unit	2 x LED, green
	switching status	LED, yellow
	switch points	LED ring, red
	function display	alphanumeric display, red 4-digit
	measured values	analogue display, 0...350° rotatable, pointer not visible when unit disconnected
	measured values	alphanumeric display, red 4-digit
With scale		yes
Extended display range (max.)	160 mbar	64.25 inH2O



Remarks	
Remarks	characteristics deviation in the extended display range: 1.5 % of the span switch point accuracy in the extended display range: 1.5 % of the span
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1 switching output
OUT2 analogue output