FLK 26/EZ-DR/1000/KONFEK - Cable

2299466

https://www.phoenixcontact.com/gb/products/2299466

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Round cable set; connection 1: IDC/FLK socket strip (1x 26-position); connection 2: IDC/FLK socket strip (1x 26-position); cable length: 10 m

Your advantages

- Unshielded

Commercial data

Item number	2299466
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DK2211
Product key	DK2211
Catalog page	Page 567 (C-5-2019)
GTIN	4017918886189
Weight per piece (including packing)	989 g
Weight per piece (excluding packing)	936 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Product properties

Product type	System cable

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation)
	-10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Cable/line

Cable length	10 m

26X0.14 [PVC]

UL AWM Style	2464/1061
Number of positions	26
Shielded	no
Cable type	26X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	26x 0.14 mm²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	8.30 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	70 mm
Smallest bending radius, movable installation	131 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)

Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Color code

black	IDC/FLK26 (1) = IDC/FLK26 (1)
brown	IDC/FLK26 (2) = IDC/FLK26 (2)
red	IDC/FLK26 (3) = IDC/FLK26 (3)
orange	IDC/FLK26 (4) = IDC/FLK26 (4)
yellow	IDC/FLK26 (5) = IDC/FLK26 (5)
green	IDC/FLK26 (6) = IDC/FLK26 (6)
blue	IDC/FLK26 (7) = IDC/FLK26 (7)
violet	IDC/FLK26 (8) = IDC/FLK26 (8)
gray	IDC/FLK26 (9) = IDC/FLK26 (9)
white	IDC/FLK26 (10) = IDC/FLK26 (10)
white-black	IDC/FLK26 (11) = IDC/FLK26 (11)
white-brown	IDC/FLK26 (12) = IDC/FLK26 (12)
white-red	IDC/FLK26 (13) = IDC/FLK26 (13)
white-orange	IDC/FLK26 (14) = IDC/FLK26 (14)
white-yellow	IDC/FLK26 (15) = IDC/FLK26 (15)
white-green	IDC/FLK26 (16) = IDC/FLK26 (16)
white-blue	IDC/FLK26 (17) = IDC/FLK26 (17)
white-violet	IDC/FLK26 (18) = IDC/FLK26 (18)
white-gray	IDC/FLK26 (19) = IDC/FLK26 (19)
brown-black	IDC/FLK26 (20) = IDC/FLK26 (20)
brown-red	IDC/FLK26 (21) = IDC/FLK26 (21)
brown-orange	IDC/FLK26 (22) = IDC/FLK26 (22)
brown-yellow	IDC/FLK26 (23) = IDC/FLK26 (23)
brown-green	IDC/FLK26 (24) = IDC/FLK26 (24)
brown-blue	IDC/FLK26 (25) = IDC/FLK26 (25)
brown-violet	IDC/FLK26 (26) = IDC/FLK26 (26)

Connection data

Connection 1

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	26
Insertion/withdrawal cycles	> 50

Pitch	2.54 mm

Connection 2

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	26
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.

Drawings

Diagram



Maximum permissible current per path in uncoiled state

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/2299466

EAC
Approval ID: RU*-DE.HB*35.B00385

UL Listed
Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

cUL Listed
Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

Classifications

ECLASS

ECLASS-13.0	27242220

ETIM

ETIM 9.0	EC000237

UNSPSC

UNSPSC 21.0	26121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk