
TT - Threaded Test Probe

mm (inch)





TT501 RA03 S

Minimum centers:	1.27 (.050)
Full travel:	5.00 (.196)
Working travel:	4.00 (.157)
Current rating:	2 - 3 A
Probe resistance:	< 20 mΩ
Plunger material:	BeCu - Gold Plated
Barrel material:	Brass - Gold Plated
Spring material:	MW - Plated

Operating temperature: -40 °C up to +80 °C
(-40 °F up to +176 °F)

Spring force at working stroke: 0.40 N (1.4 oz)

© COPYRIGHT 2024
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	NB	2025. 04. 22.
Drawed		
Checked		

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

Note


Catalog Item:
TT501 RA03 S

Drawing No.:

A4 SHEET 2 OF 1

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE

mm (inch)



Tools for the Test Probe

Tool Handle:	TH3
Adjustable Torque Handle:	TTS01
Insertion/Extraction Bit:	TBT5070

Tools for the Receptacle

Tool Handle Insertion:	TH1
Tool Handle Insertion/Extraction:	TH2
Insertion Bit:	TBR5035
Extraction Bit:	TBR5070

© COPYRIGHT 2024
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	NB	2025. 04. 22.
Drawed		
Checked		

Note

Catalog Item:
TT501 RA03 S

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE