
mm [inch]

HCT = High-Current Threaded Test Probe





HCT1600 CG05 LX

Minimum centers:	4.00 (.160)
Full travel:	5.50 (.216)
Working travel:	4.00 (.160)
Current rating:	24 A
Probe resistance:	< 10 mΩ
Plunger material:	BeCu - Gold Plated
Barrel material:	Brass - Gold Plated
Spring material:	HTA Spring

Operating temperature: -80 °C up to +250 °C
(-112 °F up to +482 °F)

Spring force at working stroke: 3.00 N (10.8 oz)

© COPYRIGHT 2019
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	V.Z.	2019.02.27.
Drawed		
Checked		

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

Note

Catalog Item: HCT1600 CG05 LX


Drawing No.:

A4 SHEET 2 OF 1

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE

mm [inch]

HCT = High-Current Threaded Test Probe



Tools for the Test Probe

Tool Handle:	TH3
Adjustable Torque Handle:	TTS01
Insertion/Extraction Bit:	TBT16071
Insertion/Extraction Bit:	TBT16072
Insertion/Extraction Bit:	TBT16073
Insertion/Extraction Bit:	TBT16090

Tools for the Receptacle

Tool Handle Insertion:	TH1
Tool Handle Insertion/Extraction:	TH2
Insertion Bit:	TBR16035
Extraction Bit:	TBR16070

© COPYRIGHT 2019
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

	Name	Date
Designed	V.Z.	2019.02.27.
Drawed		
Checked		

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

Note

Catalog Item:
HCT1600 CG05 LX

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST
TEST ▪ SUPPORT ▪ INNOVATE