

RAD-PIG-EF316-N-RSMA - Coaxial cable



2701402

<https://www.phoenixcontact.com/gb/products/2701402>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Antenna cable for control cabinet feed-through, outside diameter: 3.2 mm, inner conductor: flexible, attenuation: 0.6/0.9/1.4 dB at 0.9/2.4/5.8 GHz, N (female) -> RSMA (male), cable length: 0.5 m, technically improved successor item available: item number 1340129



Your advantages

- Halogen-free
- Flame-retardant
- UV resistant
- Oil-resistant
- For outdoor installation

Commercial data

Item number	2701402
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNN2Z2
Product key	DNN2Z2
GTIN	4046356746816
Weight per piece (including packing)	55.2 g
Weight per piece (excluding packing)	52.7 g
Customs tariff number	85442000
Country of origin	PL

RAD-PIG-EF316-N-RSMA - Coaxial cable



2701402

<https://www.phoenixcontact.com/gb/products/2701402>

Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Coaxial cable

Electrical properties

Frequency range

0.3 GHz ... 6 GHz

Impedance

50 Ω

Connection data

Connector connection

Connection method

RSMA(m)


Connector connection

Connection method

N (female)

Dimensions

Dimensional drawing



Hole diameter

16.1 mm

Material specifications

Color

signal blue (RAL 5005)

Outer sheath, material

RADOX®(LSFH)

Cable/line

Cable length

0.5 m

Cable type

EF 316

External cable diameter

2.50 mm

Outer sheath, material

RADOX®(LSFH)

External sheath, color

blue

Bending radius, long-term

12.50 mm

868 / 900 MHz

~ 0.6 dB (Attenuation of entire cable)

RAD-PIG-EF316-N-RSMA - Coaxial cable



2701402

<https://www.phoenixcontact.com/gb/products/2701402>

2.4 GHz	~ 0.9 dB (Attenuation of entire cable)
5.8 GHz	~ 1.4 dB (Attenuation of entire cable)
Resistance to oil	very good oil and chemical resistance

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Ambient temperature (assembly)	-20 °C ... 60 °C
Resistance to oil	very good oil and chemical resistance

Approvals

CE

Certificate	CE-compliant
-------------	--------------

Standards and regulations


Resistance to oil	very good oil and chemical resistance
Standard designation	Flame retardancy
Standards/specifications	DIN EN 60332-1-2
	UL 1581
Standard designation	Halogen-free
Standards/specifications	IEC 60754
Standard designation	UV resistance
Standards/specifications	IEC 60068-2-5

Mounting

Assembly note	Outdoors and indoors
---------------	----------------------

Drawings

Dimensional drawing



Drill holes

RAD-PIG-EF316-N-RSMA - Coaxial cable



2701402

<https://www.phoenixcontact.com/gb/products/2701402>

Classifications

ECLASS

ECLASS-13.0	27060310
ECLASS-15.0	27060310

ETIM

ETIM 10.0	EC001682
-----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

RAD-PIG-EF316-N-RSMA - Coaxial cable



2701402

<https://www.phoenixcontact.com/gb/products/2701402>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(b)-II, 6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-25
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b87a90b6-16c7-43c0-8dea-7ac532134310

EF3.1 Climate Change

CO2e kg	3.233 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk