

Delock Antenna Cable N plug to SMA plug LMR/CFD200 2.5 m low loss

Description

This cable connects outdoor components of the radio frequency with indoor components. The RF cable is characterized by a low attenuation.



Item no. 89420

EAN: 4043619894208

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - N plug
 - SMA plug
- Cable type: LMR/CFD200
- Attenuation:
 - 2.4 GHz: 0.55 dB per meter
 - 5.7 GHz: 0.86 dB per meter
- Impedance: 50 Ohm
- Cable diameter: 4.8 mm
- Minimum bend radius: 12,7 mm
- Colour: black
- Cable length incl. connectors: ca. 2,5 m

System requirements

- Device with a free N or SMA jack

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x N male
Connector 2:	1 x SMA plug

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	CFD200
Cable attenuation:	0.46 dB @ 1.8 GHz per meter
Cable colour:	black
Cable length incl. connectors:	2.5 m
Smallest bending radius:	12.7 mm
Cable diameter:	4.8 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

