


RoHS Compliant



ETxx02xExxxxG

No. OF POLES
02: 2 POLES
16: 16 POLES

COLOR
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

G RoHS compliant (lead<4%)
In copper Alloy
0000: "@" Logo (Standard)
000A: "ANYTEK" Mark
Any special item by customer request, please contact sales department.



REV	SIGN	DATE	DESCRIPTION	APPROVER
B		2013.11.08	The first release	Chen Bo
C	△	2018.04.11	remove the TUV safety certification	Zia

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ③ Terminal(housing): Thermoplastic (UL94V-0)
- Item ④ Terminal(cover): Thermoplastic (UL94V-0)
- Item ⑤ Clamp: Brass Ni plated
- Item ⑥ Female contact : Copper. Tin plated
- Item ⑦ Wire guard: Stainless steel
- Item ⑧ Terminal Screw: Steel , zinc plating "★" slot type

- △ Electrical: cULus
- Voltage rating: 300 V
 - Current rating: 41A
 - Wire range:
 - Solid wire(AWG): 8-24
 - Stranded wire(AWG): 8-24
 - Torque: 7 LB-In
 - Screw: M3.5
 - Wire strip length: 10-11 mm
 - Withstanding Voltage: 1.6KV
 - Operating temperature: -40°C to +115°C
 - Safety Approval: cULus
 - Critical dimension: ▲



DIM		TOL			
		2P-4P	5P-8P	9P-12P	13P-16P
Dim L	N×7.62	±0.15	±0.20	±0.30	±0.40
Dim P	(N-1)×7.62	±0.15	±0.20	±0.30	±0.40

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	ET-7.62 Series (Without Flange) "★" (Match VC three tail type series)						
PART NO.	ETxx02xExxxxG			DWG NO.	8ET0040		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Zia 2018.04.11	Chen Bo 11/08`13		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV: C	X.XX	±0.10
						X°	±1°