

Antenna Cable SMA plug > SMA jack CFD400 LLC400 3 m low loss

Description

This high-quality coaxial cable ensures a reliable connection of components of the radio frequency technology. It is characterised by a very low attenuation.



Item no. 13007

EAN: 4043619130078

Country of origin: Taiwan,
Republic of China

Package: Retail Box

Technical details

- Connectors:
1 x SMA plug >
1 x SMA jack
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: CFD400, LLC400
- Cable attenuation:
0.22 dB @ 2.4 GHz per meter
0.35 dB @ 5.7 GHz per meter
- Cable diameter: ca. 10.5 mm
- Smallest bending radius: 51.5 mm
- Cable colour: black
- Length incl. connectors (L): ca. 5 m

System requirements

- Device with a free SMA connector

Package content

- Antenna cable

Images



Interface

Connector 1:	1 x SMA plug
Connector 2:	1 x SMA jack

Technical characteristics

Impedance:	50 Ω
------------	-------------

Physical characteristics

Cable category:	coaxial
Cable type:	CFD400, LLC400
Cable attenuation:	0.22 dB @ 2.4 GHz per meter 0.35 dB @ 5.7 GHz per meter
Cable colour:	black
Cable length incl. connectors:	3 m
Smallest bending radius:	51.5 mm
Cable diameter:	10.5 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

