

# Adapter VGA male > VGA female EDID Emulator

## Description

This adapter by Delock emulates a monitor so that the signal source does not switch off the signal or change the resolution, even without a connected monitor. The adapter contains a standard set of EDID/DDC data, but it can also read and save the data of a connected monitor.



**Item no. 63326**

EAN: 4043619633265

Country of origin: China

Package: Retail Box


## Technical details

- Connectors:
  - Input:
    - 1 x VGA 15 pin male with screws >
  - Output:
    - 1 x VGA 15 pin female with nuts
    - 1 x 5 V DC jack 1.35 x 3.5 mm
- Resolution up to 2560 x 1600 @ 60 Hz (depending on the system and the connected hardware)
- DC jack for optional power supply
- 1 x LED indicator
- Plastic housing
- Colour: black
- Dimensions incl. connector (LxWxH): ca. 62 x 34 x 15 mm

## Package content

- EDID emulator
- USB power cable
- User manual

## Images



## Interface

|         |                       |
|---------|-----------------------|
| Output: | 1 x VGA 15 pin female |
| Input:  | 1 x VGA 15 pin male   |

## Technical characteristics

|                            |                     |
|----------------------------|---------------------|
| Maximum screen resolution: | 2560 x 1600 @ 60 Hz |
|----------------------------|---------------------|

## Physical characteristics

|                   |         |
|-------------------|---------|
| Housing colour:   | black   |
| Housing material: | Plastic |
| Length:           | 62 mm   |
| Width:            | 34 mm   |
| Height:           | 15 mm   |

## Manufacturer information

|             |                   |
|-------------|-------------------|
| Street      | Beeskowdamm 13/15 |
| Postal code | 14167             |
| City        | Berlin            |
| Country     | Deutschland       |
| E-Mail      | info@delock.de    |
| Website     | www.delock.de     |

