

USB Charging Cable 3 in 1 Type-A to Lightning™ / Micro USB / USB Type-C™ 30 cm black

Description

This 3 in 1 charging cable by Delock can be used for charging of different devices e.g. tablets or smartphones with Lightning™, Micro USB-B or USB Type-C™ interface through a USB power source.

Useful companion

This cable is the ideal companion for on the go e.g. on business trips or on holidays, since it combines the three most common interfaces in one cable for the latest mobile devices. This avoids annoying cable clutter and unnecessary carrying around of countless cables.

Quality and performance

The cable is very sturdy and durable due to its robust textile shielding, strong strain relief and metal housing at all cable ends. The high cable gauge of 22 AWG also supports a stable power supply of up to 3 A.



Item no. 87152

EAN: 4043619871520

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male >
 - 1 x 8 pin Apple Lightning™ male
 - 1 x USB Type Micro-B male
 - 1 x USB Type-C™ male
- Supports only charging function
- Maximum output current:
 - USB Type Micro-B / USB Type-C™: 3 A
 - Lightning™: 2.5 A
- Voltage: max. 5 V
- Cable gauge: 22 AWG
- Tinned copper conductors
- Cable with textile shielding
- Connector with metal housing
- Colour: black
- Length incl. connectors: ca. 30 cm

System requirements

- Power source with a free USB Type-A port

Package content

- Cable

Images



General

Cable finishing:	textile coating
Specification:	USB 2.0

Interface

Connector:	1 x USB 2.0 Type-A male
Connector 1:	1 x USB 2.0 Type Micro-B male
Connector 2:	1 x Apple Lightning™ male
Connector 3:	1 x USB Type-C™ male

Technical characteristics

Maximum current:	3 A
Voltage:	5 V

Physical characteristics

Housing material:	metal
Conductor material:	Copper tinned
Cable gauge:	22 AWG
Length:	30 cm
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de