




Seria wodoszczelnych obudów IP 64 od 4 do 72 m z dymionymi przezroczystymi drzwiami. Głównymi parametrami technicznymi są: odwracalne przednie i tylne panele, wymienne ramki i panele, zdejmowane drzwi o kącie otwarcia do 180° i blokadą. Obudowy mogą być wyposażone w dwubiegunowe i jednobiegunowe listwy zaciskowe, 80 A i 125 A, z okablowaniem śrubowym - pozwalają na tworzenie prostego i estetycznego okablowania, skracając czas konfiguracji obudowy.

Klasa Izolacji	II (zgodnie z normami IEC 61140)	Kolor	Szary RAL 7035
Śred. zewn. LxHxD (mm)	143x210x100	Ochrona IP	IP65
Moc rozpraszalna (W)	13	Odporność na wstrząsy	IK09
Prąd wyjściowy	400V	Liczba modułów EN 50022	4
Prąd roboczy	125 A	Próba rozżarzonym drutem	650 °C
Temperatura robocza	-25 +60 °C	Napięcia izolacji (Ui)	1000 V
Rodzaj materiału	Bezhalogenowe zgodnie z normą EN 50267-2-2	Twardość kulkowa	70 °C
Norma	EN 60670-1 (CEI 23-48) IEC60670-24 CEI 23-49	Izolacja wyjściowe	1000 V według EN 62208 zarówno przy AC, jak i DC

BEHAVIOUR WITH CHEMICAL AND ATMOSPHERIC AGENTS

Saline solution	Acids		Bases		Solvents				Mineral oil	UV rays
	Concentrated	Diluted	Concentrated	Diluted	Hexane	Benzol	Acetone	Alcohol		
Resistant	Not resistant	Limited resistance	Not resistant	Limited resistance	Limited resistance	Not resistant	Not resistant	Limited resistance	Limited resistance	Limited resistance

DIMENSIONAL



4M	GW 40 101	210	143	100	75	48	15	105	105				3	156	67
----	-----------	-----	-----	-----	----	----	----	-----	-----	--	--	--	---	-----	----


TECHNICAL SYMBOLOGY



IP
IP65

IK
IK09

GWT
650 °C



STANDARDS/APPROVALS

