






RoHS compliant



PCB Layout
tolerances +/-0.1

Product is
suitable for
Wave Solder
Process


MATERIALS

- Insulator: Thermoplastic UL 94-V-0 white
- Contact: Machined / Copper alloy
- Contact finish: Quality class 1
- Shell: steel tin plated

CHARAKTERISTICS

- Working voltage: 60V
- Current rating: 5A
- Contact resistance: max. 10mΩ - DIN41652
- Insulation resistance: >5GΩ
- Temperature range: -55° to +125°C

General tolerances (Deltron standard)				
size in mm				
> 0.5	> 3	> 6	> 30	
up to 3	up to 6	up to 30	up to 120	
tolerances				
±0.1	±0.2	±0.2	±0.3	

	All dimensions in mm	Rev.	Rev.	Rev.	DE010807		
		Rev.	Rev.	Rev.	part no.		
HD-D15SY/1				1.5:1 scale	drawn	26.10.2010	mr
					checked		
					approved		
				K060626			
Industrie NeuhoF 8c CH-3422 Kirchberg www.d-sub.swiss				drawing no.			