

RS-232 Cable Serial D-Sub9 male to female with narrow plug housing 2 m

Description

This serial cable by Delock is suitable as an **extension cable or connection cable** for modem, printer, measuring instruments, converters, RS232 hubs, patch panels etc. The cable provides the possibility of connecting adjacent systems and devices.

Mini D-Sub9 connector

These cables fit on any RS-232 port, as the **mini D-Sub9 connectors** (44 x 33.3 x 15 mm) are small and compact. In this way, RS-232 connections can be used directly adjacent to each other.



2 m

Item no. 86602

EAN: 4043619866021

Country of origin: China

Package: Zip poly bag

Technical details

- Connectors:
 - 1 x serial D-Sub9 male with screws >
 - 1 x serial D-Sub9 female with nuts
- Cable gauge: 28 AWG
- Pin assignment: 1:1
- Colour: black
- Insulator: PVC
- Screw type: #4-40 UNC
- Cable diameter: ca. 5 mm
- Cable length incl. connectors: ca. 2 m

System requirements

- A free D-Sub9 female
- A free D-Sub9 male port

Package content

- Cable

Images



General

Specification:	RS-232 (EIA / TIA)
Style:	Connection- / Extensioncable Mini Sub-D9

Interface

Connector 1:	1 x serial Sub-D 9 male with screws
Connector 2:	1 x serial Sub-D 9 female with nuts

Technical characteristics

Data transfer rate:	921.6 Kbps
Signal transmission:	TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND

Physical characteristics

Cable type:	AWM Style 2464 28 AWG 80 °C 300 V VW-1
Cable length incl. connectors:	2 m
Pin finishing:	gold-plated
Conductor material:	Copper tinned
Cable gauge:	28 AWG
Screw type:	#4-40 UNC
Colour:	black
Cable diameter:	5 mm
Cable jacket material:	PVC
Safety of Flammability:	VW-1

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland

E-Mail	info@delock.de
Website	www.delock.de