

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1708072008

Status:


Active

Overview:

NeoScale Mezzanine System

Description:

NeoScale High-Speed Mezzanine Plug, 2.80mm Pitch, 6x12, 72 Triads-100 Ohm (216 Circuits), 12.00mm Connector Height



Series image - Reference only

Documents:	
3D Model (PDF)	Packaging Specification PK-170807-002-001 (PDF)
Drawing (PDF)	Datasheet (PDF)
3D Model	RoHS Certificate of Compliance (PDF)
Product Specification PS-170807-0001-001 (PDF)	

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	170807
Application	Board-to-Board, Signal
Overview	NeoScale Mezzanine System
Product Name	NeoScale
UPC	887191540757
Physical	
Breakaway	No
Circuits (Loaded)	216
Circuits (maximum)	216
Color - Resin	Black
Durability (mating cycles max)	100
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	13.967/g
Number of Rows	6
Orientation	Vertical
PCB Locator	Yes
PCB Retention	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.80mm
Pitch - Termination Interface	2.80mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Robotic Placement	Pick and Place Cap
Shrouded	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Solder or Weld

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV	Green Image Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
170807 Series

Mates With
NeoScale High-Speed Mezzanine
Receptacle 1708142008 , 1708142016

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	30V AC (RMS)

Solder Process Data

Duration at Max. Process Temperature (seconds)	020
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Electrical Model Document	EE-170807-2020, EE-170807-2030
Packaging Specification	PK-170807-002-001
Product Specification	PS-170807-0001-001
S-Parameter Model	SP-170807-2020, SP-170807-2030
Sales Drawing	SD-170807-2016, SD-170807-2026

This document was generated on 05/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION