


OID254



Photoelectric distance sensor

OIDLCPKG/US



Product characteristics		
Type of light		red light
Laser protection class		1
Application		
Special feature		Background suppression
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	75; (24 V)
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	650
Typ. lifetime	[h]	50000
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Inputs		
Input circuit of digital inputs		1 x 24 V PNP; (IEC 61131-2 Typ 3)
Outputs		
Total number of outputs		2
Electrical design		PNP
Number of digital outputs		2
Output function		normally open / normally closed; (complementary)
Max. current load per output	[mA]	100
Switching frequency DC	[Hz]	11
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Max. light spot diameter	[mm]	5
Light spot dimensions refer to		2 m



Photoelectric distance sensor

OIDLCPKG/US

Detection range hysteresis	[%]	< 5
Note on monitoring range hysteresis		black 6% remission
Background suppression available		yes
Background suppression	[m]	< 20

Measuring/setting range		
Measuring range	[m]	0.03...2
Sampling rate	[Hz]	33

Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1
SDCI standard		IEC 61131-9
Profiles		Smart Sensor: Sensor Identification; Binary Data Channel; Process Value; Sensor Diagnosis
SIO mode		yes
Process data analogue		1
Process data binary		1
Min. process cycle time	[ms]	6.6
Supported DeviceIDs	Type of operation	DeviceID
	default	579

Operating conditions		
Ambient temperature	[°C]	-25...60
Note on ambient temperature		at ta < -10 °C warm-up is necessary, laser is off
Protection		IP 65; IP 67; IP 68; IP 69K

Tests / approvals		
EMC	EN 60947-5-2	
Laser protection class		1
Notes on laser protection	Caution:	laser light
	laser class:	1
		EN / IEC60825-1:2007
		EN / IEC60825-1:2014
		Complies with 21 CFR 1040 except for deviations pursuant to Laser Notice No. 50, dated June 2007.
MTTF	[years]	210
UL approval	power supply	Class 2
	File number UL	E174191

Mechanical data		
Weight	[g]	217.15
Dimensions	[mm]	M30 x 1.5 / L = 85
Thread designation		M30 x 1.5
Materials		housing: stainless steel; front pane: PMMA; PEI; EPDM

OID254



Photoelectric distance sensor

OIDLCPKG/US

Displays / operating elements

Display	switching status	LED, yellow switching output 1
	operation	LED, green
Display unit		cm

Accessories


Items supplied	lock nuts: 2 x M30, stainless steel
----------------	-------------------------------------

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection



4: OUT / IO-Link




Photoelectric distance sensor

OIDLCPKG/US

Diagrams and graphs

hysteresis graph



x: distance [mm]

y: Hysteresis [mm]

1 = object black 6% remission

2 = object white 90% remission