

Adapter USB 2.0 Type-A to 1 x Serial RS-232 D-Sub 9 pin male with ferrite core 0.25 m

Description

This adapter by Delock enables the connection of a serial device via USB Type-A port. The additional ferrite core on the cable prevents interference signals and improves data transmission.



Item no. 64276

EAN: 4043619642762

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
 - 1 x USB 2.0 Type-A male
 - 1 x serial RS-232 DB9 male with screws
- Chipset: CH343G
- 1 x ferrite core
- Screw type: #4-40 UNC
- Compatible with USB 3.0, USB 2.0, and USB 1.1
- Signals: TxD, RxD, RTS, CTS, DTR, DSR, DCD, RI, GND
- Data transfer rate up to 460.8 Kbps
- Colour: black
- Cable length incl. connectors: ca. 0.25 m


System requirements

- Windows 10/10-64/11
- PC or laptop with a free USB Type-A port

Package content

- USB Type-A to 1 x serial adapter
- User manual

Images



General

Function:	Plug & Play
Specification:	RS-232 (EIA / TIA) USB 1.1 USB 2.0
Supported operating system:	Linux Kernel 2.6 or above Mac OS 10.9 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows Server 2008 R2 Windows Server 2012 R2 Windows Server 2012 Windows Server 2016 Windows Server 2019 Windows 11 Windows Server 2022

Interface

Connector 1:	1 x USB 2.0 Type-A male
Connector 2:	1 x serial Sub-D 9 male with screws

Technical characteristics

Chipset:	WCH CH343G
Data transfer rate:	460.8 Kbps
Signal transmission:	TxD, Rx/D, RTS, CTS, DTR, DSR, DCD, RI, GND
Data transmission:	asynchronous full duplex Half duplex Bidirectional
UART:	USB to serial UART

Physical characteristics

Ferrite core:	1 x
Cable colour:	black
Cable length incl. connectors:	0.25 m
Pin finishing:	gold-plated
Screw type:	#4-40 UNC
Shielding:	double
Colour:	black

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de