

Antenna Cable RP-TNC jack bulkhead to I-PEX Inc., MHF® I plug 1.37 20 cm splash proof

Description

The antenna cable by Delock is suitable for connecting components of radio frequency technology.

Through an inside located groove embedded in the base plate and the seal on the RP-TNC base, a splash-proof connection to a device is achieved.



Item no. 88464

EAN: 4043619884643

Country of origin: Taiwan,
Republic of China

Package: Zip poly bag

Technical details

- Connectors:
1 x RP-TNC female bulkhead
1 x I-PEX Inc., MHF® I plug
- Impedance: 50 Ohm
- Cable: coaxial
- Cable type: 1.37
- Cable attenuation: 2.5 dB @ 2.4 GHz per meter
- Cable colour: black
- Smallest bending radius: 9 mm
- Cable length incl. connectors: ca. 20 cm

System requirements

- Device with one free RP-TNC or I-PEX Inc., MHF® I port

Package content

- Cable
- Locking ring, nut, gasket

Images



Interface

Connector 1:	1 x RP-TNC female bulkhead
Connector 2:	1 x I-PEX Inc., MHF® I plug

Technical characteristics

Impedance:	50 Ω
------------	------

Physical characteristics

Cable category:	coaxial
Cable type:	1.37
Cable attenuation:	2.5 dB @ 2.4 GHz per meter
Cable colour:	black
Cable length incl. connectors:	20 cm
Smallest bending radius:	9 mm
Cable diameter:	1.37 mm

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de

