


P/N LEGEND


A2013	WR	XP	N	0	X	T1	N	K0	G
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩

① Series No.
② Connector type: WR=Right angle
③ No. of circuits
④ N=Halogen Free
⑤ Material: 0=Nylon 66-V0
⑥ Color: W=White , B=Black
⑦ Plating code for contacts: T1=Tin-plated
⑧ Plating code: N=Non-plating
⑨ Option code: K0=With pin kink
⑩ Packing code: G=Bag


04~15P




03P




02P







P.C.B LAYOUT

SPECIFICATIONS
Current Rating: 4A AC,DC
Voltage Rating: 125V AC,DC
Temperature Range: -40℃ ~ +105℃
Contact Resistance: 10mΩ Max.
Insulation Resistance: 1000MΩ Min.
Withstanding Voltage: 1000V AC/minute







MATED CONDITION

Circuit No.	Dimensions A	Dimensions B	Circuit No.	Dimensions A	Dimensions B
02P	2.00	5.96	09P	16.00	19.96
03P	4.00	7.96	10P	18.00	21.96
04P	6.00	9.96	11P	20.00	23.96
05P	8.00	11.96	12P	22.00	25.96
06P	10.00	13.96	13P	24.00	27.96
07P	12.00	15.96	14P	26.00	29.96
08P	14.00	17.96	15P	28.00	31.96

REV.	DESCRIPTION	DATE	NAME
A3	EN202411071818	2024.11.07	樊翠鳳
A2	EN1303050065	2013.03.04	周傑亮
A1	EN1302160047	2013.02.16	郭木思
A0	NEW RELEASE	2012.08.15	陳敏

燦達電子工業股份有限公司
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT	SCALE	SHEET
mm	1 : 1	1 of 1

DRAWN BY	APPROVED BY
陳敏	董正一
2012.08.15	2012.08.15

GENERAL TOLERANCE
X.X±0.25
X.XX±0.15
X.XXX±0.05
ANGLE±

TITLE:
2.00mm PITCH
90°WAFER

DRAW NO.: A2013WR-XPNXXXXXXX
REV. A3