

Adapter USB Type-C™ to 1 x Serial RS-422/485 male with 6 pin terminal block 5 V 0.5 m

Description

This USB Type-C™ 2.0 to serial adapter by Delock provides a standard RS-422 and RS-485 connection for measuring devices, POS systems, printers, modems, IoT devices etc.

Terminal block

The terminal block is suitable for installation in PC housings and for any solderless cable connection with RS-422 or RS-485 interface.

Power supply

Optionally, external devices can be supplied with voltage of 5 V over the terminal block.



Item no. 64266

EAN: 4043619642663

Country of origin: China

Package: Retail Box

Technical details

- Connectors:
Adapter:
1 x USB Type-C™ 2.0 male
1 x serial RS-422/485 D-Sub 9 pin male with screws
Terminal block:
1 x serial RS-422/485 D-Sub 9 pin female with nuts
1 x 6 pin terminal block
- Terminal block: T/R+, T/R-, RXD+, RXD-, GND, VCC
- Chipset: FTDI FT232R
- Data transfer rate up to 921.6 Kbps
- Cable length incl. connectors: ca. 0.5 m


System requirements

- Linux Kernel 5.11 or above
- Mac OS 11.6 or above
- Windows 8.0.5.1-64/10/10-64/11
- Windows Server 2019
- PC or laptop with a free USB Type-C™ port

Package content

- USB 2.0 to 1 x serial RS-422/485 adapter
- Terminal block adapter
- User manual

Images



G3403	DB9 Buchse/Male		Terminalblock/Terminal Block
	RS-422	RS-485	
PIN	RS-422	RS-485	RS-422/RS-485
1	Transmit (A+)	T/R (A+)	T/R (A+)
2	Transmit (B-)	T/R (B-)	T/R (B-)
3	Receive (A+)	NC	Receive (A+)
4	Receive (B-)	NC	Receive (B-)
5	Signal GND (SG)	Signal GND (SG)	Signal GND (SG)
6	USB 5 V	USB 5 V	USB 5 V
7	NC	NC	NC
8	NC	NC	NC
9	NC	NC	NC



General

Function:	Plug & Play
Specification:	RS-422 / RS-485 (EIA / TIA) USB 2.0
Supported operating system:	Linux Kernel 2.6 or above Windows 10 32-Bit Windows 10 64-Bit Windows 8.1 32-Bit Windows 8.1 64-Bit Windows Server 2012 R2 Windows Server 2016 Windows Server 2019 Mac OS 11.1 or above Windows 11
Protection:	ESD (Electrostatic Discharge)

Interface

Connector 1:	1 x USB Type-C™ 2.0 male
Connector 2:	1 x Serial RS-422/485 DB9 male
Connector 3:	1 x 6 Pin Terminal Block

Technical characteristics

Chipset:	FTDI FT232RL
FIFO:	1 x 128 byte receive 1 x 256 byte transmit
Signal transmission:	T/R+, T/R-, RXD+, RXD-, GND, VCC
Data transmission:	asynchronous full duplex Half duplex Bidirectional differential
Voltage supply:	5 V output voltage
UART:	USB to serial UART

Support:	Modbus
----------	--------

Physical characteristics

Housing colour:	black
Cable colour:	transparent
Cable length incl. connectors:	0.5 m
Screw type:	#4-40 UNC
Shielding:	double

Manufacturer information

Street	Beeskowdamm 13/15
Postal code	14167
City	Berlin
Country	Deutschland
E-Mail	info@delock.de
Website	www.delock.de