
ST - ICT test probe

mm [inch]



ST500 LA53 M

Minimum centers:	1.27 [.050]
Full travel:	6.35 [.250]
Working travel:	4.00 [.157]
Current rating:	2-3 A
Probe resistance:	< 20mΩ
Operating temperature:	-40°C up to +120°C
Plunger material:	Steel / Gold plated
Barrel material:	PhBr / Gold plated
Spring material:	Stainless Steel

Spring force at working stroke:1.5 N [5.4 oz]

© COPYRIGHT 2024
EQUIP-TEST KFT.
ALL RIGHTS RESERVED

This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2024.06.04
Drawed		
Checked		
Note		


Catalog Item: **ST500 LA53 M**

Drawing No.:

A4 SHEET 1 OF 2

EQUIP TEST
TEST - SUPPORT - INNOVATE

ST - ICT test probe



Tools for the Test Probe

Tool Handle:	TH1
Universal Insertion Bit:	TBP7500
Insertion Bit:	TBP5070

Tools for the Receptacle

Tool Handle Insertion:	TH1
Universal Insertion Bit:	TBP7500
Insertion Bit:	TBR5035
Extraction Bit:	TBR5070

© COPYRIGHT 2024
EQUIP-TEST KFT.
ALL RIGHTS RESERVED
This drawing, model, intellectual product belongs to Equip-Test Kft. Forwarding it to 3rd. party, copying it or using for any other purpose without the written approval of Equip-Test Kft., could entail to legal and criminal procedure!

	Name	Date
Designed	M.K.	2024.06.04
Drawed		
Checked		
Note		

Catalog Item: **ST500 LA53 M**

Drawing No.:

A4 SHEET 2 OF 2

EQUIPTEST™ TEST · SUPPORT · INNOVATE