

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Round cable set; controller: Mitsubishi Electric MELSEC L, MELSEC Q, Honeywell MasterLogic ML200; connection 1: Fujitsu connector (1x 40-position); connection 2: IDC/FLK socket strip (4x 14-position); cable length: 3 m

Commercial data

Item number	2903505
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DK226M
Product key	DK226M
Catalog page	Page 483 (C-5-2019)
GTIN	4046356745437
Weight per piece (including packing)	617.1 g
Weight per piece (excluding packing)	627.1 g
Customs tariff number	85444290
Country of origin	DE

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Supported controller MITSUBISHI MELSEC Q

Suitable I/O card	QX41
	QX41-S1
	QX42
	QX42-S1
	QY41P
	QY42P
	QH42P
	QY82P

Supported controller MITSUBISHI MELSEC L

Suitable I/O card	LX41C4
	LX42C4
	LY41NT1P
	LY42NT1P
	LY41PT1P
	LY42PT1P

Supported controller HONEYWELL MasterLogic 200

Suitable I/O card	2MLQ-TR4A
	2MLQ-TR8A
	2MLQ-TR4B
	2MLQ-TR8B

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Cable/line

Cable length	3 m
10X0.14 [PVC]	
UL AWM Style	2464/1061
Number of positions	10
Shielded	no
Cable type	10X0.14 [PVC]
Conductor type	Round cable set
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	10x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	6.10 mm ±0.4 mm
Outer sheath, material	Semi-rigid PVC
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	52 mm
Smallest bending radius, movable installation	98 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000
Halogen-free	no
Flame resistance	IEC 60332-1-2 (raw cable)
	VDE 0842, Part 332-1-2 (raw cable)
	IEC 60332-3-22 (raw cable)
	UL VW-1
	CSA FT-1
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Splitting cable for four modules

Color code

black	Fujitsu40 (B20) = IDC/FLK14-1 (1)
brown	Fujitsu40 (B19) = IDC/FLK14-1 (2)
red	Fujitsu40 (B18) = IDC/FLK14-1 (3)
orange	Fujitsu40 (B17) = IDC/FLK14-1 (4)
yellow	Fujitsu40 (B16) = IDC/FLK14-1 (5)
green	Fujitsu40 (B15) = IDC/FLK14-1 (6)
blue	Fujitsu40 (B14) = IDC/FLK14-1 (7)
violet	Fujitsu40 (B13) = IDC/FLK14-1 (8)
gray	Fujitsu40 (B1) = IDC/FLK14-1 (9)
white	Fujitsu40 (A1) = IDC/FLK14-1 (10)
black	Fujitsu40 (B12) = IDC/FLK14-2 (1)
brown	Fujitsu40 (B11) = IDC/FLK14-2 (2)

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

red	Fujitsu40 (B10) = IDC/FLK14-2 (3)
orange	Fujitsu40 (B9) = IDC/FLK14-2 (4)
yellow	Fujitsu40 (B8) = IDC/FLK14-2 (5)
green	Fujitsu40 (B7) = IDC/FLK14-2 (6)
blue	Fujitsu40 (B6) = IDC/FLK14-2 (7)
violet	Fujitsu40 (B5) = IDC/FLK14-2 (8)
gray	Fujitsu40 (B1) = IDC/FLK14-2 (9)
white	Fujitsu40 (A1) = IDC/FLK14-2 (10)
black	Fujitsu40 (A20) = IDC/FLK14-3 (1)
brown	Fujitsu40 (A19) = IDC/FLK14-3 (2)
red	Fujitsu40 (A18) = IDC/FLK14-3 (3)
orange	Fujitsu40 (A17) = IDC/FLK14-3 (4)
yellow	Fujitsu40 (A16) = IDC/FLK14-3 (5)
green	Fujitsu40 (A15) = IDC/FLK14-3 (6)
blue	Fujitsu40 (A14) = IDC/FLK14-3 (7)
violet	Fujitsu40 (A13) = IDC/FLK14-3 (8)
gray	Fujitsu40 (B2) = IDC/FLK14-3 (9)
white	Fujitsu40 (A2) = IDC/FLK14-3 (10)
black	Fujitsu40 (A12) = IDC/FLK14-4 (1)
brown	Fujitsu40 (A11) = IDC/FLK14-4 (2)
red	Fujitsu40 (A10) = IDC/FLK14-4 (3)
orange	Fujitsu40 (A9) = IDC/FLK14-4 (4)
yellow	Fujitsu40 (A8) = IDC/FLK14-4 (5)
green	Fujitsu40 (A7) = IDC/FLK14-4 (6)
blue	Fujitsu40 (A6) = IDC/FLK14-4 (7)
violet	Fujitsu40 (A5) = IDC/FLK14-4 (8)
gray	Fujitsu40 (B2) = IDC/FLK14-4 (9)
white	Fujitsu40 (A2) = IDC/FLK14-4 (10)

Connection data

Connection 1

Connection method	Fujitsu connector
Type	FCN 367
Number of connections	1
Number of positions	40
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	4
Number of positions	14
Insertion/withdrawal cycles	> 50

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Pitch	2.54 mm
-------	---------

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable




2903505
<https://www.phoenixcontact.com/gb/products/2903505>

Drawings

Connection diagram

Socket strip (X1)	Double assignment	Conductor color	FLK 14 (X2) Byte 0	FLK 14 (X3) Byte 1	FLK 14 (X4) Byte 2	FLK 14 (X5) Byte 3
PIN B20		Black	PIN 1			
PIN B19		Brown	PIN 2			
PIN B18		Red	PIN 3			
PIN B17		Orange	PIN 4			
PIN B16		Yellow	PIN 5			
PIN B15		Green	PIN 6			
PIN B14		Blue	PIN 7			
PIN B13		Violet	PIN 8			
PIN B01		Gray	PIN 9			
PIN A01		White	PIN10			
PIN B12		Black		PIN 1		
PIN B11		Brown		PIN 2		
PIN B10		Red		PIN 3		
PIN B09		Orange		PIN 4		
PIN B08		Yellow		PIN 5		
PIN B07		Green		PIN 6		
PIN B06		Blue		PIN 7		
PIN B05		Violet		PIN 8		
		Gray		PIN 9		
		White		PIN10		
PIN A20		Black			PIN 1	
PIN A19		Brown			PIN 2	
PIN A18		Red			PIN 3	
PIN A17		Orange			PIN 4	
PIN A16		Yellow			PIN 5	
PIN A15		Green			PIN 6	
PIN A14		Blue			PIN 7	
PIN A13		Violet			PIN 8	
PIN B02		Gray			PIN 9	
PIN A02		White			PIN10	
PIN A12		Black				PIN 1
PIN A11		Brown				PIN 2
PIN A10		Red				PIN 3
PIN A09		Orange				PIN 4
PIN A08		Yellow				PIN 5
PIN A07		Green				PIN 6
PIN A06		Blue				PIN 7
PIN A05		Violet				PIN 8
		Gray				PIN 9
		White				PIN10



Maximum permissible current per path in uncoiled state

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2903505>



EAC

Approval ID: RU*-DE.HB*35.B00385

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Classifications

ECLASS

ECLASS-13.0	27242220
-------------	----------

ETIM

ETIM 9.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

CABLE-FCN40/4X14/ 3,0M/IM/MEL - Cable



2903505

<https://www.phoenixcontact.com/gb/products/2903505>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0ede557b-379c-4b5a-bfb8-39e667f90d47

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk