



ProLight PZ2C-1FxE-2
PZ2C-1FPE-A2
1W Power LED
Technical Datasheet
Version: 1.0

ProLight Opto PZ2C Series


Features

- Industry-compatible size : 2.8 x 3.5 x 0.65 mm
- 3-V configuration
- RoHS compliant

Main Applications

- Warning Light
- Indoor lighting
- Outdoor lighting
- Architectural

Mechanical Dimensions



Notes:

1. The cathode side of the device is denoted by the chamfer on the part body.
2. Drawing not to scale.
3. All dimensions are in millimeters.
4. Unless otherwise indicated, tolerances are $\pm 0.1\text{mm}$.
5. Please do not solder the emitter by manual hand soldering, otherwise it will damage the emitter.
6. **Please do not use a force of over 0.3kgf impact or pressure on the lens of the LED, otherwise it will cause a catastrophic failure.**

*The appearance and specifications of the product may be modified for improvement without notice.

Flux Characteristics, $T_j = 25^{\circ}\text{C}$

Radiation Pattern	Color	Part Number Emitter	Luminous Flux Φ_v (lm)		
			@150mA Min.	Typ.	Refer @350mA Typ.
Lambertian	White	PZ2C-1FWE-2	70	83	182
	Blue	PZ2C-1FBE-2	18	22	43
	PC Amber	PZ2C-1FPE-A2	60	67	146

- ProLight maintains a tolerance of $\pm 7\%$ on flux and power measurements.
- Please do not drive at rated current more than 1 second without proper heat sink.

Electrical Characteristics, $T_j = 25^{\circ}\text{C}$

Color	Min.	Forward Voltage V_F (V)			Thermal Resistance Junction to Solder Pad ($^{\circ}\text{C/W}$)
		@150mA Typ.	Max.	Refer @350mA Typ.	@150mA Typ.
White	2.60	2.85	3.20	3.10	5
Blue	2.60	2.80	3.20	3.09	5
PC Amber	2.60	2.85	3.20	3.10	6

- ProLight maintains a tolerance of $\pm 0.1\text{V}$ for Voltage measurements.

Optical Characteristics at 150mA, $T_j = 25^{\circ}\text{C}$

Color	Dominant Wavelength λ_D , or Color Temperature CCT			Viewing Angle (FWHM, degrees)
	Min.	Typ.	Max.	Typ.
White	5000 K	5650 K	6450 K	120
Blue	470 nm	475 nm	480 nm	120
PC Amber	588.5 nm	590 nm	591.5 nm	120

- ProLight maintains a tolerance of $\pm 1\text{nm}$ for dominant wavelength measurements.
- ProLight maintains a tolerance of $\pm 5\%$ for CCT measurements.

Electro-Optical Characteristics, $T_j = 25^{\circ}\text{C}$

I_F (mA)	V_F (V)	Power (W)	PZ2C-1FWE-2		PZ2C-1FPE-A2	
			Flux (lm)	lm/W	Flux (lm)	lm/W
55	2.71	0.15	31.5	211.2	25.5	170.9
100	2.78	0.28	56.3	202.7	45.6	163.9
150	2.85	0.43	83.0	194.2	67.0	156.7
200	2.92	0.58	108.7	186.5	87.7	150.4
250	2.98	0.74	133.8	179.6	107.7	144.7
300	3.04	0.91	157.9	173.1	127.3	139.5
350	3.10	1.09	181.5	167.2	145.9	134.4

I_F (mA)	V_F (V)	Power (W)	PZ2C-1FBE-2	
			Flux (lm)	lm/W
55	2.62	0.14	9.3	64.5
100	2.71	0.27	15.7	57.9
150	2.80	0.42	22.0	52.4
200	2.88	0.58	28.0	48.6
250	2.95	0.74	33.2	45.0
300	3.02	0.91	38.3	42.2
350	3.09	1.08	43.3	40.1

● All values are reference only.

Absolute Maximum Ratings

Parameter	White/Blue/PC Amber
Max DC Forward Current (mA)	350
Peak Pulsed Forward Current (mA)	400 (less than 1/10 duty cycle@1KHz)
ESD Sensitivity (HBM per MIL-STD-883E Method 3015.7)	$\pm 2000\text{V}$
LED Junction Temperature	125°C
Operating Temperature	$-40^{\circ}\text{C} - 105^{\circ}\text{C}$
Storage Temperature	$-40^{\circ}\text{C} - 105^{\circ}\text{C}$
Reverse Voltage	Not designed to be driven in reverse bias
Moisture Sensitivity Rating	MSL 3

Photometric Luminous Flux Bin Structure at 150mA

Color	Bin Code	Minimum Photometric Flux (lm)	Maximum Photometric Flux (lm)	Available Color Bins
White	T1	70	80	All
	T2	80	90	[1]
	U1	90	100	[1]
Blue	N1	18	21	All
	N2	21	24	[1]
	P1	24	28	[1]
	P2	28	33	[1]
PC Amber	S2	60	70	All
	T1	70	80	[1]

- ProLight maintains a tolerance of $\pm 7\%$ on flux and power measurements.
- The flux bin of the product may be modified for improvement without notice.
- ^[1] The rest of color bins are not 100% ready for order currently. Please ask for quote and order possibility.

Dominant Wavelength Bin Structure at 150mA

Color	Bin Code	Minimum Dominant Wavelength (nm)	Maximum Dominant Wavelength (nm)
Blue	3	470	475
	4	475	480

- ProLight maintains a tolerance of $\pm 1\text{nm}$ for dominant wavelength measurements.

Note: Although several bins are outlined, product availability in a particular bin varies by production run and by product performance. Not all bins are available in all colors.


Forward Voltage Bin Structure at 150mA

Color	Bin Code	Minimum Voltage (V)	Maximum Voltage (V)
White	E	2.6	2.8
	F	2.8	3.0
	G	3.0	3.2
Blue	E	2.6	2.8
	F	2.8	3.0
	G	3.0	3.2
PC Amber	E	2.6	2.8
	F	2.8	3.0
	G	3.0	3.2

- ProLight maintains a tolerance of $\pm 0.1\text{V}$ for Voltage measurements.

Color Bin

White Binning Structure Graphical Representation



Color Bin


White Bin Structure

Bin Code	x	y	Typ. CCT (K)	Bin Code	x	y	Typ. CCT (K)
V2	0.3376	0.3616	5155	W2	0.3207	0.3462	5830
	0.3464	0.3688			0.3292	0.3539	
	0.3452	0.3558			0.3293	0.3423	
	0.3371	0.3493			0.3215	0.3353	
V3	0.3371	0.3493	5155	W3	0.3215	0.3353	5830
	0.3452	0.3558			0.3293	0.3423	
	0.3441	0.3428			0.3294	0.3306	
	0.3366	0.3369			0.3222	0.3243	
W1	0.3292	0.3539	5475	X1	0.3123	0.3385	6240
	0.3376	0.3616			0.3207	0.3462	
	0.3371	0.3493			0.3215	0.3353	
	0.3293	0.3423			0.3136	0.3283	
W4	0.3293	0.3423	5475	X4	0.3136	0.3283	6240
	0.3371	0.3493			0.3215	0.3353	
	0.3366	0.3369			0.3222	0.3243	
	0.3294	0.3306			0.3150	0.3180	

- Tolerance on each color bin (x , y) is ± 0.005

Color Bin

PC Amber Binning Structure Graphical Representation




PC Amber Bin Structure

Bin Code	x	y	Typ. CCT (K)
2	0.5523	0.4271	-
	0.5687	0.4107	
	0.5838	0.4156	
	0.5662	0.4331	


- Tolerance on each color bin (x , y) is ± 0.005

Color Spectrum, $T_c = 25^\circ\text{C}$


1. White



2. Blue




3. PC Amber




Light Output Characteristics

1. Relative Light Output vs. Junction Temperature at 150mA






2. Junction Temperature vs. Relative Forward Voltage at 150mA






Forward Current Characteristics, $T_j = 25^{\circ}\text{C}$

1. Forward Voltage vs. Forward Current




Forward Current Characteristics, $T_j = 25^\circ\text{C}$


2. Forward Current vs. Normalized Relative Luminous Flux



Cathode Solder Pad Temperature vs. Maximum Forward Current



Typical Representative Spatial Radiation Pattern



Moisture Sensitivity Level - JEDEC Level 3

Level	Floor Life		Soak Requirements			
			Standard		Accelerated Environment	
	Time	Conditions	Time (hours)	Conditions	Time (hours)	Conditions
3	168 hours	$\leq 30^{\circ}\text{C}$ / 60% RH	192 +5/-0	30°C / 60% RH	40 +1/-0	60°C / 60% RH

- The standard soak time includes a default value of 24 hours for semiconductor manufacture's exposure time (MET) between bake and bag and includes the maximum time allowed out of the bag at the distributor's facility.
- Table below presents the moisture sensitivity level definitions per IPC/JEDEC's J-STD-020C.

Level	Floor Life		Soak Requirements			
			Standard		Accelerated Environment	
	Time	Conditions	Time (hours)	Conditions	Time (hours)	Conditions
1	Unlimited	$\leq 30^{\circ}\text{C}$ / 85% RH	168 +5/-0	85°C / 85% RH	NA	NA
2	1 year	$\leq 30^{\circ}\text{C}$ / 60% RH	168 +5/-0	85°C / 60% RH	NA	NA
2a	4 weeks	$\leq 30^{\circ}\text{C}$ / 60% RH	696 +5/-0	30°C / 60% RH	120 +1/-0	60°C / 60% RH
3	168 hours	$\leq 30^{\circ}\text{C}$ / 60% RH	192 +5/-0	30°C / 60% RH	40 +1/-0	60°C / 60% RH
4	72 hours	$\leq 30^{\circ}\text{C}$ / 60% RH	96 +2/-0	30°C / 60% RH	20 +0.5/-0	60°C / 60% RH
5	48 hours	$\leq 30^{\circ}\text{C}$ / 60% RH	72 +2/-0	30°C / 60% RH	15 +0.5/-0	60°C / 60% RH
5a	24 hours	$\leq 30^{\circ}\text{C}$ / 60% RH	48 +2/-0	30°C / 60% RH	10 +0.5/-0	60°C / 60% RH
6	Time on Label (TOL)	$\leq 30^{\circ}\text{C}$ / 60% RH	Time on Label (TOL)	30°C / 60% RH	NA	NA

Qualification Reliability Testing

Stress Test	Stress Conditions	Stress Duration	Failure Criteria
Room Temperature Operating Life (RTOL)	25°C, $I_F = \text{max DC}$ (Note 1)	1000 hours	Note 2
Wet High Temperature Operating Life (WHTOL)	85°C/60%RH, $I_F = \text{max DC}$ (Note 1)	1000 hours	Note 2
Wet High Temperature Storage Life (WHTSL)	85°C/85%RH, non-operating	1000 hours	Note 2
High Temperature Storage Life (HTSL)	110°C, non-operating	1000 hours	Note 2
Low Temperature Storage Life (LTSL)	-40°C, non-operating	1000 hours	Note 2
Non-operating Temperature Cycle (TMCL)	-40°C to 120°C, 30 min. dwell, <5 min. transfer	200 cycles	Note 2
Mechanical Shock	1500 G, 0.5 msec. pulse, 5 shocks each 6 axis		Note 3
Natural Drop	On concrete from 1.2 m, 3X		Note 3
Variable Vibration Frequency	10-2000-10 Hz, log or linear sweep rate, 20 G about 1 min., 1.5 mm, 3X/axis		Note 3
Solder Heat Resistance (SHR)	260°C $\pm$ 5°C, 10 sec.		Note 3
Solderability	Steam age for 16 hrs., then solder dip at 260°C for 5 sec.		Solder coverage on lead

Notes:

1. Depending on the maximum derating curve.
2. Criteria for judging failure


Item	Test Condition	Criteria for Judgement	
		Min.	Max.
Forward Voltage (V_F)	$I_F = \text{max DC}$	--	Initial Level x 1.1
Luminous Flux or Radiometric Power (Φ_V)	$I_F = \text{max DC}$	Initial Level x 0.7	--
Reverse Current (I_R)	$V_R = 5V$	--	50 μA

* The test is performed after the LED is cooled down to the room temperature.


3. A failure is an LED that is open or shorted.

Recommended Solder Pad Design

Solder Pad




Stencil Pattern



- All dimensions are in millimeters.


Reflow Soldering Condition

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Average Ramp-Up Rate (T_{Smax} to T_p)	3°C / second max.	3°C / second max.
Preheat – Temperature Min (T_{Smin}) – Temperature Max (T_{Smax}) – Time (t_{Smin} to t_{Smax})	100°C 150°C 60-120 seconds	150°C 200°C 60-180 seconds
Time maintained above: – Temperature (T_L) – Time (t_l)	183°C 60-150 seconds	217°C 60-150 seconds
Peak/Classification Temperature (T_p)	240°C	260°C
Time Within 5°C of Actual Peak Temperature (t_p)	10-30 seconds	20-40 seconds
Ramp-Down Rate	6°C/second max.	6°C/second max.
Time 25°C to Peak Temperature	6 minutes max.	8 minutes max.



- We recommend using the M705-S101-S4 solder paste from SMIC (Senju Metal Industry Co., Ltd.) for lead-free soldering.
- Do not use solder pastes with post reflow flux residue>47%. (58Bi-42Sn eutectic alloy, etc) This kind of solder pastes may cause a reliability problem to LED.
- All temperatures refer to topside of the package, measured on the package body surface.
- Repairing should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used. It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.
- Reflow soldering should not be done more than three times.
- When soldering, do not put stress on the LEDs during heating.
- After soldering, do not warp the circuit board.


Emitter Reel Packaging



Note:

1. Tolerance unless mentioned is $\pm 0.1\text{mm}$; unit = mm.

Emitter Reel Packaging



Notes:

1. Empty component pockets sealed with top cover tape.
2. Drawing not to scale.
3. Tolerance unless mentioned is $\pm 0.3\text{mm}$; unit = mm.
4. 4000 pieces per reel.

Moisture Sensitivity

We recommend keeping LEDs in the provided, resealable moisture-barrier packaging (MBP) until immediately prior to soldering. Unopened MBP that contains LEDs do not need special storage for moisture sensitivity.

Once the MBP is opened, LEDs should be handled and stored as MSL 3 per JEDEC J-STD-033, meaning they have limited exposure time before damage to the LED may occur during the soldering operation. The table on the right specifies the maximum exposure time in days depending on temperature and humidity conditions. LEDs with exposure time longer than the specified maximums must be baked according to the baking conditions listed below.

Moisture Sensitivity Level	Temp.	Maximum Percent Relative Humidity				
		50%	60%	70%	80%	90%
Level 3	35 °C	8	5	1	0.5	0.5
Level 3	30 °C	11	7	1	1	1
Level 3	25 °C	14	10	2	1	1
Level 3	20 °C	20	13	2	1	1

Baking Conditions

It is not necessary to bake all LEDs. Only the LEDs that meet all of the following criteria must be baked:

- 1.LEDs that have been removed from the original MBP.
- 2.LEDs that have been exposed to a humid environment longer than listed in the Moisture Sensitivity section above.
- 3.LEDs that have not been soldered.

LEDs should be baked at 60 °C for 24 hours. LEDs may be baked in the original reels. Remove LEDs from the MBP before baking. Do not bake parts at temperatures higher than 60 °C. This baking operation resets the exposure time as defined in the Moisture Sensitivity section above.



Precaution for Use

- Storage
Please do not open the moisture barrier bag (MBB) more than one week. This may cause the leads of LED discoloration. We recommend storing ProLight's LEDs in a dry box after opening the MBB. The recommended storage conditions are temperature 5 to 30°C and humidity less than 40% RH. It is also recommended to return the LEDs to the MBB and to reseat the MBB.
- The slug is not electrically neutral. Therefore, we recommend to isolate the heat sink.
- **We recommend using the M705-S101-S4 solder paste from SMIC (Senju Metal Industry Co., Ltd.) for lead-free soldering.**
- **Do not use solder pastes with post reflow flux residue > 47%. (58Bi-42Sn eutectic alloy, etc) This kind of solder pastes may cause a reliability problem to LED.**
- Any mechanical force or any excess vibration shall not be accepted to apply during cooling process to normal temperature after soldering.
- Please avoid rapid cooling after soldering.
- Components should not be mounted on warped direction of PCB.
- Repairing should not be done after the LEDs have been soldered. When repairing is unavoidable, a heat plate should be used. It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.
- This device should not be used in any type of fluid such as water, oil, organic solvent and etc. When cleaning is required, isopropyl alcohol should be used.
- When the LEDs are illuminating, operating current should be decided after considering the package maximum temperature.
- The appearance, specifications and flux bin of the product may be modified for improvement without notice. Please refer to the below website for the latest datasheets.
<http://www.prolightopto.com/>

Handling of Silicone LEDs

Notes for handling of silicone LEDs

- Please do not use a force of over 0.3kgf impact or pressure on the silicone, otherwise it will cause a catastrophic failure.
- The LEDs should only be picked up by making contact with the sides of the LED body.
- Avoid touching the silicone especially by sharp tools such as Tweezers.
- Avoid leaving fingerprints on the silicone.
- Please store the LEDs away from dusty areas or seal the product against dust.
- When populating boards in SMT production, there are basically no restrictions regarding the form of the pick and place nozzle, except that mechanical pressure on the silicone lens must be prevented.
- Please do not mold over the silicone lens with another resin. (epoxy, urethane, etc)



Disclaimers

ProLightopto Technology has made every reasonable effort to ensure the accuracy of the information in this datasheet. However, it should be understood that this information is for guidance only and does not constitute any offer or part of a contract.

ProLightopto Technology does not guarantee or accept any legal liability for the accuracy, completeness, or usefulness of any information, product, technology, or process disclosed in this datasheet. The company reserves the right to make changes or improvements to this datasheet at its discretion.

Unless this datasheet is incorporated into a formal contract, customers should not rely on the information as a binding commitment to any specifications or product parameters by ProLightopto Technology. Customers are advised to verify that the information is current and complete before entering into any contract or acknowledging any purchase order. Therefore, all products described herein are subject to ProLightopto Technology's terms and conditions at the time of order acknowledgment.

Unless agreed upon by contractual agreement, not all parameters of each product are necessarily tested. ProLightopto Technology does not warrant or grant any license, either expressed or implied, under its patent rights or the rights of others.

Reproduction of the information contained herein is permitted only if done without any modifications or alterations. Altering this information and reproducing it is considered an unfair and deceptive business practice. ProLightopto Technology is not responsible or liable for any such altered documentation.

Reselling ProLightopto Technology's products with statements that differ from or exceed the parameters specified by ProLightopto Technology voids all express or implied warranties for the associated product or service and is considered an unfair and deceptive business practice. ProLightopto Technology is not responsible or liable for any such statements.

ProLightopto Technology's products are not authorized for use as critical components in life support devices or systems without explicit written approval from ProLightopto Technology.

For the purposes of this disclaimer :

1. Life support devices or systems are defined as those intended for surgical implant into the body or those that support or sustain life. Their failure, when used according to instructions for use provided in the labeling, can reasonably be expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure can reasonably be expected to cause the failure of the device or system, or to affect its safety or effectiveness.